Microvalves \emptyset 4 and manual operating devices Microvalves \emptyset 4, 3/2 normally open and normally closed




Standard executions				
Version	Symbol	Code	Item	
Normally open	3 1	030251	AM04132A	
Normally closed	3 1	030252	AM04132C	
Normally open with side connections	3 1	030253	AM04132AL	
Normally closed with side connections	2	030254	AM04132CL	




Series of poppet microvalves arranged for operating manually. Connections with integral 4 mm push-in fittings.

According to the application you can choose between the version with bottom connections or with side ones.

For the choice of the operating device see page 2.265.1.





Technical data			
Fluid	Compressed filtered air with or without lubrication. Lubrication, if started, must be continued.		
Pressure range	0 ÷ 8 bar		
Temperature range	-20 °C ÷ + 80 °C		
Operating force	5 N		
Flow	80 NI/min.		
Connections	With integral 4 mm push-in fittings		
Fixing	Through 2 holes (Ø 4 mm) on the body Through 1 hole (Ø 22 mm) on panel (with operating device mounted)		
Mounting	In any position		
Materials	Body: Acetal resin Seals: Nitrile rubber (NBR)		